



TYPE APPROVAL CERTIFICATE

Certificate No:
TAE000019N
Revision No:
4

This is to certify:

That the Electric Power Cable

with type designation(s)

AFUMEX FIRS NAU-XTCUA 0,6/1 kV,
AFUMEX FIRS NAU-XTA 0,6/1 kV,
AFUMEX FIRS NAU-XOTCUA 0,6/1 kV

Issued to

PRYSMIAN CABLES SPAIN, S.A.
Vilanova i la Geltrú, Barcelona, Spain

is found to comply with

DNV rules for classification – Ships, offshore units, and high speed and light craft

Application :

General power and lighting. Control.

Products approved by this certificate are accepted for installation on all vessels classed by DNV GL.

Type	Rated voltage (kV)	Temp. class (°C)
AFUMEX FIRS NAU-XTCUA 0,6/1 kV	0,6/1	90
AFUMEX FIRS NAU-XTA 0,6/1 kV	0,6/1	90
AFUMEX FIRS NAU-XOTCUA 0,6/1 kV	0,6/1	90

Issued at **Høvik** on **2023-07-01**

for **DNV**

This Certificate is valid until **2028-06-30**.

DNV local unit: **Area NB/CMC Iberia**

Approval Engineer: **Ivar Bull**

.....
Frederik Tore Elter
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



Form code: TA 251

Revision: 2022-12

www.dnv.com

Page 1 of 3

Product description

Type:	AFUMEX FIRS NAU-XTCUA 0,6/1 kV	0,6/1
	AFUMEX FIRS NAU-XTA 0,6/1 kV	0,6/1
	AFUMEX FIRS NAU-XOTCUA 0,6/1 kV	0,6/1

Construction:

Conductors:	Plain or tinned, stranded copper. Class 2 or class 5
Core insulation:	Mica-tape + HF XLPE
Inner covering:	Tape or Halogen free compound
Metallic screen:	Overall metallic screen. Helically copper tape overlapped (XOTCUA)
Armour:	Plain or tinned copper wire braid (TCU) or Galv. steel wire braid (T)
Outer sheath:	SHF1

AFUMEX FIRS NAU-XTCUA & AFUMEX FIRS NAU-XTA 0,6/1 kV:

Number of cores	Conductor cross section [mm ²]
1	1, 1.5, 2.5, 4, 6, 10, 16, 25, 35, 50, 70, 95, 120, 150, 185, 240, 300
2, 4	1, 1.5, 2.5, 4, 6, 10, 16, 25, 35, 50, 70, 95, 120
3	1, 1.5, 2.5, 4, 6, 10, 16, 25, 35, 50, 70, 95, 120, 150, 185
5	1, 1.5, 2.5, 4, 6, 10, 16, 25, 35, 50, 70
7, 10, 12, 14, 16, 19, 20, 24, 27, 30, 37	1.5, 2.5

AFUMEX FIRS NAU-XOTCUA & AFUMEX FIRS NAU-XTA 0,6/1 kV

Number of cores	Conductor cross section [mm ²]
3G	2.5, 4, 6, 10

Application/Limitation

This type of cable is fire resistant in accordance with IEC Publication 60331.

The requirements of SOLAS Amendments Chapter II-1, Part D, Reg. 45, 5.2 (provision to be taken to limit Fire Propagation along Bunches of Cables or Wires) are fulfilled without any additional measures.

Type Approval documentation

Data sheets: [AFUMEX FIRS NAU XTCUA 0,6/1kV \(power\) rev.10](#)
[AFUMEX FIRS NAU XTCUA 0,6/1kV \(control\) rev.8](#)
[AFUMEX FIRS NAU XOTCUA 0,6/1kV Rev.7](#)

Test reports: [di_25388 dated 13/09/2016](#)

Tests carried out

Standard	Release	General description	Limitation
DNV CP-0399	2021-08	Electric cables.	
IEC 60092-350	2020-01	Electrical installations in ships - Part 350: General construction and test methods of power, control and instrumentation cables for shipboard and offshore applications	
IEC 60092-360	2021-01	Electrical installations in ships - Part 360: Insulating and sheathing materials for shipboard and offshore units, power, control, instrumentation and telecommunication cables	
IEC 60092-353	2016-09	Electrical installations in ships - Part 353: Power cables for rated voltages 1 kV and 3 kV	
IEC 60331-1/2	2018-03	Tests for electric cables under fire conditions - Circuit integrity - Part 1: Test method for fire with shock at a temperature of at least 830 °C for cables of rated voltage up to and including 0,6/1,0 kV	120 min+ 15 min cooling down time

Standard	Release	General description	Limitation
IEC 60331-21	1999-04	Tests for electric cables under fire conditions – Circuit integrity – Part 21: Procedures and requirements – Cables of rated voltage up to and including 0,6/1,0 kV	120 min+ 15 min cooling down time
IEC 60332-3-22	2018-07	Tests on electric and optical fibre cables under fire conditions - Part 3-22: Test for vertical flame spread of vertically mounted bunched wires or cables - Category A	
IEC 60754-1	2019-11	Test on gases evolved during combustion of materials from cables - Part 1: Determination of the halogen acid gas content	Low Halogen: <0,5% Halogen
IEC 60754-2	2019-11	Test on gases evolved during combustion of materials from cables - Part 1: Determination of the halogen acid gas content	Halogen free: pH > 4,3 Conductivity < 10µS/mm
IEC 61034-1/2	2019-11	Measurement of smoke density of cables burning under defined conditions – Part 1: Test apparatus Part 2: Test procedure and requirements	Low smoke Light transmittance >60%

Marking of product

PRYSMIAN SAP – AFUMEX FIRS NAU XTCUA or XTA or NAU-XOTCUA - size - 0,6/1 kV – 60092-353 – IEC 60331-1/2 – IEC 60332-3-22 - Lot No. or

SAP = Santa Perpetua Plant.

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine tests (RT) and selected type tests (ref. to applicable class programs) checked (if not available these tests shall be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer’s product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE